


Through-beam sensor receiver

OGE-HPKG/US



Product characteristics

Type of light	red light
Housing	threaded type

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	8
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	645

Outputs

Electrical design	PNP
Output function	light-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Overload protection	yes

Detection zone

Transmitter / receiver	receiver
Range [m]	< 8
Range adjustable	no

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67; (in conjunction with a corresponding connector)



Through-beam sensor receiver

OGE-HPKG/US

Tests / approvals

EMC	EN 60947-5-2	
MTTF	[years]	1335

Mechanical data

Weight	[g]	14.4
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 44
Thread designation		M18 x 1
Materials		housing: ABS
Lens material		PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A



Connection

