


OU5007



Through-beam sensor receiver

OUE-HPKG



receiver in upper lens



Product characteristics		
Type of light		infrared light
Housing		rectangular
Dimensions	[mm]	28 x 16 x 51
Application		
Function principle		Through-beam sensor
Electrical data		
Operating voltage	[V]	10...55 DC
Current consumption	[mA]	20; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880
Outputs		
Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	140
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Transmitter / receiver		receiver
Range	[m]	< 6
Range adjustable		yes
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67


OU5007



Through-beam sensor receiver

OUE-HPKG

Tests / approvals		
EMC	EN 60947-5-2 EN 55011	class B
MTTF [years]	618	
Mechanical data		
Weight [g]	150	
Housing	rectangular	
Dimensions [mm]	28 x 16 x 51	
Materials	PPO modified	
Lens material	glass	
Lens alignment	side lens	
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Accessories (supplied)	Angle bracket: 1 x, E20211	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 2 m, PVC; 3 x 0.34 mm ²		
Connection		



BN	brown
BU	blue
BK	black



Through-beam sensor receiver

OUE-HPKG

Diagrams and graphs

excess gain graph

