# **EVC005**

# Connecting cable with socket

ADOAH040MSS0005H04



# Please see the technical note under "Downloads" M12x1 See The technical note under "Downloads"



Application		
Special feature		Free from silicone; Halogen-free; Gold-plated contacts; Drag chain suitability
Free from silicone		yes
Electrical data		
Operating voltage	[V]	< 250 AC / < 300 DC
Protection class		II
Max. current load total	[A]	4
Operating conditions		
Ambient temperature	[°C]	-2590
Note on ambient temperature		cULus:75
Ambient temperature (moving)	[°C]	-2590
Note on ambient temperature (moving)		cULus:75
Storage temperature	[°C]	-2555
Storage humidity	[%]	10100
Other climatic conditions for storage according to stated class		1K22/ DIN 60721-3-1
Protection		IP 65; IP 67; IP 68; IP 69K
Mechanical data		
Weight	[g]	154.9
Dimensions	[mm]	26.5 x 15.5 x 36.5

# **EVC005**

## Connecting cable with socket





Moulded-body material	TPU		
Material nut	brass, nickel-plated		
Sealing material	FKM		
Drag chain suitability	yes		
Drag chain suitability	bending radius for flexible use	min. 10 x cable diameter	
	travel speed	max. 3.3 m/s for a horizontal travel length of 5 m and max. acceleration of 5 m/s <sup>2</sup>	
	bending cycles	> 5 Mio.	
	torsional strain	± 180 °/m	

Remarks		
Notes	Please see the technical note under "Downloads"	
Pack quantity	1 pcs.	

### **Electrical connection**


Cable: 5 m, PUR, Halogen-free, black, Ø 4.3 mm;  $4 \times 0.34$  mm<sup>2</sup> ( $42 \times Ø 0.1$  mm)

### Electrical connection - socket

Connector: 1 x M12, angled; coding: A; Moulded body: TPU, orange; Locking: brass, nickel-plated; Sealing: FKM; Contacts: gold-plated; Tightening torque: 0.6...1.5 Nm



### Connection



Core colours : black

 BK =
 black

 BN =
 brown

 BU =
 blue

 WH =
 white

# **EVC005**


# Connecting cable with socket

ADOAH040MSS0005H04



# Diagrams and graphs

characteristic line for derating



Derating Imax \* 0.8 (DIN EN 60512-5-2)

- X Ambient temperature [°C]
- Y Current [A]