


# O7E200



## Through-beam sensor receiver

O7E-DPKG/0,20M/AS



receiver in upper lens



### Product characteristics

Type of light	red light
Housing	rectangular

### Application

Function principle	Through-beam sensor
--------------------	---------------------

### Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	10; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light

### Outputs

Electrical design		PNP
Output function		dark-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	1000
Short-circuit protection		yes
Type of short-circuit protection		pulsed

### Detection zone

Transmitter / receiver		receiver
Range	[m]	0...1.5
Range adjustable		no
Light spot dimensions refer to		at maximum range

# O7E200



## Through-beam sensor receiver

O7E-DPKG/0,20M/AS

### Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65

### Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	1312

### Mechanical data

Weight	[g]	14.5
Housing		rectangular
Dimensions	[mm]	20.3 x 15 x 9
Materials		PA
Lens material		PMMA
Lens alignment		side lens

### Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------


### Remarks

Remarks	operating voltage "supply class 2" according to UL	
Pack quantity	1 pcs.	

### Electrical connection

Cable: 0.2 m, PUR; 3 x 0.14 mm<sup>2</sup>

Connector: 1 x M8; coding: A; Locking: snap-fit



### Connection

