


Flow monitor

SID10ABB100G/US-100-IAZ

Article no longer available - archive entry



- 1 internal thread M18 x 1.5
2 setting pushbuttons



Product characteristics

Number of inputs and outputs	Number of analogue outputs: 1
Process connection	M18 x 1,5 internal thread

Application

Media	Liquids
Medium temperature [°C]	-25...80
Pressure rating [bar]	30

Liquids

Medium temperature [°C]	-25...80
-------------------------	----------

Electrical data

Operating voltage [V]	20...36 DC; (to SELV/PELV ; with reference to UL: "limited voltage" with overcurrent protection in accordance with UL508)
Current consumption [mA]	90; (without load)
Reverse polarity protection	yes
Power-on delay time [s]	15; (optically indicated)

Inputs / outputs

Number of inputs and outputs	Number of analogue outputs: 1
------------------------------	-------------------------------

Outputs

Total number of outputs	1
Output signal	analogue signal
Number of analogue outputs	1



Flow monitor

SID10ABB100G/US-100-IAZ

Analogue current output	[mA]	4...20
Max. load	[Ω]	500
Overload protection		yes

Measuring/setting range

Liquids		
Setting range	[cm/s]	3...60

Response times

Response time	[s]	1...10
---------------	-----	--------

Liquids		
Response time	[s]	1...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

Shock resistance	DIN IEC 68-2-27	50 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	20 g (55...2000 Hz)

Mechanical data

Dimensions	[mm]	M18 x 1.5
Thread designation		M18 x 1.5
Materials		PBT-GF20
Materials (wetted parts)		stainless steel (316L/1.4404); O-ring: FPM 8 x 1,5 gr 80° Shore A
Process connection		M18 x 1,5 internal thread

Displays / operating elements

Display	function	10 x LED, 2-colour
---------	----------	--------------------

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; coding: A



Flow monitor

SID10ABB100G/US-100-IAZ

Connection

