


# AC1310



## AS-Interface Modbus/TCP gateway with PLC

ControllerE 2Mstr EN RS232

Article no longer available - archive entry



Application	
Application	decentralised controller; EtherNet/IP gateway; web server
Electrical data	
Operating voltage [V]	24 DC; (operating voltage "supply class 2" according to cULus)
Current consumption [mA]	< 700
Max. current consumption from AS-i [mA]	10
Max. power consumption [VA]	10
Number of AS-i masters	2
Interfaces	
Communication interface	RS232; Ethernet
Ethernet	
Transmission rate	10; 100
Protocol	Modbus TCP; TCP/IP
Usage type	data transmission

# AC1310



## AS-Interface Modbus/TCP gateway with PLC

ControllerE 2Mstr EN RS232

RS232	
Number of R232 interfaces	1
Transmission rate	9600...115200 Baud
Connector type	RJ11
Usage type	programming
Addition	electrically isolated

Operating conditions	
Ambient temperature [°C]	0...60
Storage temperature [°C]	-20...70
Max. relative air humidity [%]	95
Protection	IP 20


AS-i classification	
AS-i version	2.1
AS-i profile	M3
AS-i certificate	61110

Mechanical data	
Housing	housing for DIN rail mounting
Materials	aluminium; steel sheet galvanised

Displays / operating elements		
Display	function	4 x LED, red
		5 x LED, green
		3 x LED, yellow
		full graphic LCD display

Remarks	
Pack quantity	1 pcs.

Electrical connection	
Connection	



Article no longer available - archive entry