




Fibre optic through beam sensor

FE-30-A-A-M6/2M



Application	
Function principle	Through-beam sensor
Detection zone	
Range with fibre optic amplifier type	OIF
OIF	
Range of fibre optics [mm]	240
Operating conditions	
Ambient temperature [°C]	-40...290
Mechanical data	
Weight [g]	201
Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	2000
Min. bending radius [mm]	30; (for fixed installation)
Fibre arrangement	●
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	aluminium

E20219



Fibre optic through beam sensor

FE-30-A-A-M6/2M

Accessories	
Accessories (supplied)	hexagon nuts: 2 x M6, stainless steel
	tooth lock washers: 2
	knurled nut: 1 x M30
Remarks	
Pack quantity	1 pcs.