


SU8621

Ultrasonic flow meter

SUN11XFBFRKG/US



ACS CE PA cUL US LISTED IO-Link KTW/W270 Reg31

Product characteristics

Measuring range	1...240 l/min	0.06...14.4 m³/h	16...3804 gph	0.26...63.4 gpm
Process connection	1" NPT DN25 external thread			

Application

Special feature	Gold-plated contacts	
Media	ultra-pure water; water; hydrous media	
Note on media	hydrous media: for media with >10 % additives, the repeatability is the only available value	
Medium temperature	-20...100 °C	-4...212 °F
Min. bursting pressure	150 bar	15 MPa
Pressure rating	100 bar	10 MPa
Vacuum resistance [mbar]	-1000	
MAWP (for applications according to CRN) [bar]	100	

Electrical data

Operating voltage [V]	18...32 DC; (to SELV/PELV)			
Current consumption [mA]	< 75			
Protection class	III			
Reverse polarity protection	yes			
Power-on delay time [s]	5			
Measuring principle	ultrasonic			



Ultrasonic flow meter

SUN11XFBFRKG/US

Inputs				
Inputs		counter reset		
Outputs				
Total number of outputs		2		
Output signal		switching signal; pulse signal; analogue signal; IO-Link; frequency signal; diagnostic signal; totaliser switching signal		
Electrical design		PNP/NPN		
Output function		normally open / normally closed; (parameterisable)		
Max. voltage drop switching output DC	[V]	2		
Permanent current rating of switching output DC	[mA]	100		
Switching frequency DC	[Hz]	0...10000		
Analogue current output	[mA]	4...20		
Max. load	[Ω]	500		
Pulse output		flow rate meter		
Short-circuit protection		yes		
Type of short-circuit protection		pulsed		
Overload protection		yes		
Measuring/setting range				
Measuring range		1...240 l/min	0.06...14.4 m³/h	16...3804 gph 0.26...63.4 gpm
Display range		-288...288 l/min	-17.28...17.28 m³/h	-4565...4565 gph -76.08...76.08 gpm
Resolution		0.1 l/min	0.001 m³/h	1 gph 0.02 gpm
Set point SP		2.3...240 l/min	0.139...14.4 m³/h	37...3804 gph 0.61...63.4 gpm
Reset point rP		1.1...238.8 l/min	0.064...14.325 m³/h	17...3784 gph 0.28...63.07 gpm
Analogue start point ASP		-240...192 l/min	-14.4...11.522 m³/h	-3804...3044 gph -63.4...50.73 gpm
Analogue end point AEP		-191.9...240 l/min	-11.511...14.4 m³/h	-3041...3804 gph -50.68...63.4 gpm
Low flow cut-off LFC		1...12 l/min	0.06...0.72 m³/h	16...190 gph 0.26...3.17 gpm
Frequency end point, FEP		48.1...240 l/min	2.889...14.4 m³/h	763...3804 gph 12.72...63.4 gpm
Frequency at the end point FRP	[Hz]	1...10000		
Volumetric flow quantity monitoring				
Pulse length	[s]	0.002...2		
Pulse value		0.02...99990000 l; 0.005...26414563.515 gal		
Temperature monitoring				
Measuring range		-20...100 °C		-4...212 °F
Display range		-44...124 °C		-47.2...255.2 °F
Resolution		0.1 °C		0.1 °F
Set point SP		-19.6...100 °C		-3.2...212 °F
Reset point rP		-20...99.6 °C		-4...211.2 °F
Analogue start point		-20...76 °C		-4...168.8 °F
Analogue end point		4...100 °C		39.2...212 °F
Frequency start point, FSP		-20...76 °C		4...168.8 °F
Frequency end point, FEP		4...100 °C		4...168.8 °F
Frequency at the end point FRP	[Hz]	1...10000		



Ultrasonic flow meter

SUN11XFBFRKG/US

Accuracy / deviations		
Flow monitoring		
Accuracy (in the measuring range)		$\pm (1,0 \% \text{ MW} + 0,5 \% \text{ MEW})$
Repeatability		$\pm 0,2 \% \text{ MEW}$
Temperature monitoring		
Accuracy [K]		$\pm 2,5 (Q > 5 \% \text{ MEW})$
Temperature coefficient [% of the span / 10 K]		0,2
Response times		
Flow monitoring		
Response time [s]		$< 0,25; (dAP = 0, T09)$
Damping process value dAP [s]		0...5
Temperature monitoring		
Dynamic response T05 / T09 [s]		5,7 / 86
Software / programming		
Diagnostic functions		direction of flow detection; signal quality
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1.3
SDCI standard		IEC 61131-9: 2013-07
Profiles		Identification and Diagnosis (0x4000)
Required master port type		A
Process data analogue		3
Process data binary		2
Min. process cycle time [ms]		9.6
IO-Link process data (cyclical)	function	bit length
	totaliser	32
	Flow monitoring	32
	Temperature monitoring	32
	status	4
	Output 1	1
	Output 2	1
Supported DeviceIDs	Type of operation	DeviceID
	default	1463
Operating conditions		
Ambient temperature [°C]		-20...60
Storage temperature [°C]		-25...80
Protection		IP 67
Tests / approvals		
EMC	DIN 61326-1:2021	
CPA approval	model number	002US
	accuracy class	1,5
Shock resistance	DIN IEC 68-2-27	20 g (11ms)

SU8621



Ultrasonic flow meter

SUN11XFBFRKG/US

Vibration resistance	DIN IEC 68-2-6	5 g (10...2000Hz)
MTTF [years]		160
UL approval	UL Approval no.	J034
	File number UL	E174189
Pressure Equipment Directive	can be used for group 2 fluids; group 1 fluids on request	

Mechanical data

Weight [g]	631.5
Type of mounting	inlet pipe length 5xDN; outlet pipe length 1xDN
Materials	housing: stainless steel (1.4404 / 316L); Display: PFA; Sealing Display: FKM; connector: POKAN
Materials (wetted parts)	Pipe section: stainless steel (1.4404 / 316L); Process connection sealing: Centellen Flat seal
Process connection	1" NPT DN25 external thread
Surface characteristics Ra/Rz of the wetted parts	49.21 µin

Displays / operating elements

Display	colour display 1,44", 128 x 128 pixels
Switching function	2 x LED, yellow
diagnosis	1 x LED, three-colour

Accessories

Items supplied	Flat seal 2, Centellen package insert
----------------	--

Remarks

Remarks	MW = measured value
	MEW = Final value of the measuring range
	pulse and totaliser signal are only available for one of the two outputs
	the accuracy indications are adhered to over the entire application area
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated





Ultrasonic flow meter

SUN11XFBFRKG/US

Connection



OUT1/IO-Link: switching output volumetric flow quantity monitoring
switching output Temperature monitoring
Pulse output quantity meter
frequency output volumetric flow quantity monitoring
frequency output Temperature monitoring
signal output Preset counter


OUT2/InD: switching output volumetric flow quantity monitoring
switching output Temperature monitoring
Pulse output quantity meter
analogue output flow
analogue output temperature
signal output Preset counter
input counter reset

colours to DIN EN 60947-5-2

Core colours
BK= black
BN= brown
BU= blue
WH= white

Diagrams and graphs

Note on pressure loss




SU8621

Ultrasonic flow meter

SUN11XFBFRKG/US



derating ambient temperature



- 1 Ambient temperature
- 2 Medium temperature