

OF5030




Through-beam sensor receiver

OFE-FPKG/10M

Article no longer available - archive entry

Alternative article: OF5019 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Type of light	infrared light
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 60

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 25
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light

Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	320
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

Detection zone

Transmitter / receiver	receiver
Range [m]	< 4

Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67



OF5030



Through-beam sensor receiver

OFE-FPKG/10M

Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF [years]		990
Mechanical data		
Weight [g]		0.237
Housing		threaded type
Dimensions [mm]		M12 x 1 / L = 60
Thread designation		M12 x 1
Materials		brass nickel-plated
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Accessories		
Accessories (supplied)		lock nuts: 2 x
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 10 m, PUR; 3 x 0.34 mm ²		
Connection		



Core colours :

- BN = brown
- BU = blue
- BK = black

OF5030




Through-beam sensor receiver

OFE-FPKG/10M

Diagrams and graphs

excess gain graph



Article no longer available - archive entry

Alternative article: OF5019 When selecting an alternative article and accessories please note that technical data may differ! – When selecting an alternative article and accessories please note that technical data may differ!