


# RB6058



## Incremental encoder with solid shaft

RB-0060-I24/S

Article no longer available - archive entry



- 1 reference mark
- 2 M3 Depth 5 mm



### Product characteristics

|                     |               |
|---------------------|---------------|
| Resolution          | 60 resolution |
| Shaft design        | solid shaft   |
| Shaft diameter [mm] | 6             |

### Electrical data

|                          |            |
|--------------------------|------------|
| Operating voltage [V]    | 10...30 DC |
| Current consumption [mA] | 150        |

### Outputs

|                                   |        |
|-----------------------------------|--------|
| Electrical design                 | HTL    |
| Max. current load per output [mA] | 50     |
| Switching frequency [kHz]         | 160    |
| Type of short-circuit protection  | < 60 s |
| Phase difference A and B [°]      | 90     |

### Measuring/setting range

|            |               |
|------------|---------------|
| Resolution | 60 resolution |
|------------|---------------|

### Operating conditions

|                                |           |
|--------------------------------|-----------|
| Ambient temperature [°C]       | -20...70  |
| Storage temperature [°C]       | -30...100 |
| Max. relative air humidity [%] | 98        |
| Protection                     | IP 64     |

### Tests / approvals

|                      |                     |
|----------------------|---------------------|
| Shock resistance     | 100 g (6 ms)        |
| Vibration resistance | 10 g (55...2000 Hz) |

# RB6058



## Incremental encoder with solid shaft

RB-0060-I24/S


| Mechanical data                               |                 |
|---|-----------------|
| Dimensions [mm]                               | Ø 36.5 / L = 38 |
| Materials                                     | aluminium       |
| Max. revolution, mechanical [U/min]           | 10000           |
| Max. starting torque [Nm]                     | 1               |
| Reference temperature torque [°C]             | 20              |
| Shaft design                                  | solid shaft     |
| Shaft diameter [mm]                           | 6               |
| Shaft material                                | steel (1.4104)  |
| Max. shaft load axial (at the shaft end) [N]  | 5               |
| Max. shaft load radial (at the shaft end) [N] | 10              |

## Electrical connection

Cable: ,3 m, PUR

|        |                  |
|--------|------------------|
| 1      | 0V B             |
| 2      | n.c.             |
| 3      | 0 index          |
| 4      | 0V 0 index       |
| 5      | A                |
| 6      | 0V A             |
| 7      | failure inverted |
| 8      | B                |
| 9      | n.c.             |
| 10     | 0V               |
| 11     | n.c.             |
| 12     | 10...30V         |
| Screen | housing          |

Connector: 1 x M23 (ifm 1001.6)



# RB6058




## Incremental encoder with solid shaft

RB-0060-I24/S

### Diagrams and graphs

Pulse diagram



Output A

Output B

0 index

Article no longer available - archive entry