




## Retro-reflective sensor

OFR-FPKG

Article no longer available - archive entry

replaced by: OF5014



### Product characteristics

Type of light	infrared light
Housing	threaded type
Dimensions [mm]	M12 x 1 / L = 60

### Application

Function principle	Retro-reflective sensor
--------------------	-------------------------

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 30
Protection class	II
Reverse polarity protection	yes
Type of light	infrared light
Wave length [nm]	880

### Outputs

Electrical design	PNP
Output function	light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	400
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

### Detection zone

Range [m]	< 2; (Prismatic reflector Ø 80 E20005)
Range referred to prismatic reflector [m]	0.05...2; (Prismatic reflector Ø 80 E20005)

### Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67



# OF5038



## Retro-reflective sensor

OFR-FPKG

Mechanical data		
Housing		threaded type
Dimensions [mm]		M12 x 1 / L = 60
Thread designation		M12 x 1
Materials		brass white bronze coated
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
	operation	1 x LED, green
Accessories		
Accessories (supplied)		lock nuts: 2 x
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.34 mm <sup>2</sup>		
Connection		



Core colours :

- BN = brown
- BU = blue
- BK = black

Article no longer available - archive entry

replaced by: OF5014