


O6S215



Through-beam sensor transmitter

O6SIOOKG/AS/4P



1: light emission



Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Through-beam sensor
--------------------	---------------------

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	11; ((24 V))
Protection class		III
Type of light		infrared light
Wave length	[nm]	850

Detection zone

Transmitter / receiver		transmitter
Range	[m]	< 15
Max. light spot diameter	[mm]	460
Light spot dimensions refer to		at maximum range

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 65; IP 67

Tests / approvals

EMC		EN 60947-5-2
MTTF	[years]	2920
UL approval		UL Approval no. E002



Through-beam sensor transmitter

O6SIOOKG/AS/4P

Mechanical data		
Weight	[g]	17.7
Housing		rectangular
Dimensions	[mm]	35.4 x 13 x 21
Materials		housing: ABS; PPSU
Lens material		PMMA
Lens alignment		side lens
Sealing material		EPDM
Tightening torque	[Nm]	0.5

Displays / operating elements		
Display	operation	1 x LED, green


Remarks		
Remarks		operating voltage "supply class 2" according to cULus
Pack quantity		1 pcs.

Electrical connection

Connector: 1 x M8; coding: A; Locking: metal, coated; Sealing: EPDM



Connection



Through-beam sensor transmitter

O6SI00KG/AS/4P

Diagrams and graphs

excess gain graph

