




Incremental encoder with solid shaft

RB-0100-I24/L2F

Article no longer available - archive entry



- 1 reference mark
2 M3 Depth 5 mm



Product characteristics

Resolution	200 resolution
Shaft design	solid shaft
Shaft diameter [mm]	6

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	150

Outputs

Electrical design	HTL
Max. current load per output [mA]	50
Switching frequency [kHz]	160
Type of short-circuit protection	< 60 s
Phase difference A and B [°]	90

Measuring/setting range

Resolution	200 resolution
------------	----------------

Operating conditions

Ambient temperature [°C]	-30...70
Storage temperature [°C]	-30...100
Max. relative air humidity [%]	98
Protection	IP 50

Tests / approvals

Shock resistance	100 g (6 ms)
Vibration resistance	10 g (55...2000 Hz)

Mechanical data

Dimensions [mm]	Ø 36.5 / L = 38
Materials	aluminium

RB6034



Incremental encoder with solid shaft

RB-0100-I24/L2F

Max. revolution, mechanical [U/min]	10000
Max. starting torque [Nm]	1
Reference temperature torque [°C]	20
Shaft design	solid shaft
Shaft diameter [mm]	6
Shaft material	steel (1.4104)
Max. shaft load axial (at the shaft end) [N]	5
Max. shaft load radial (at the shaft end) [N]	10


Electrical connection

Cable: 2 m, PUR; radial, can also be used axially

white/green	0V
brown/green	L+
brown	A
green	0V A
grey	B
pink	0V B
red	0 index
black	0V 0 index
lilac	failure inverted
screen	housing

Diagrams and graphs

Pulse diagram



direction of rotation clockwise (looking at the shaft)