


# AC1007



## AS-Interface PLC

Contr 1MSTR 1RS485

Article no longer available - archive entry



1 serial interface RS485



### Application

Application mini-controller for signal preprocessing

### Electrical data

Operating voltage	[V]	22...30 DC; (24 DC; to PELV)
Insulation rating	[V]	500
Max. current consumption from AS-i	[mA]	80
Max. power consumption	[VA]	10
Electrical separation		yes

### Outputs

Electrical design AS-i

### Interfaces

#### RS232

Transmission rate	4800...62400 Baud
Connector type	SUB-D

### Operating conditions

Ambient temperature	[°C]	0...60
Storage temperature	[°C]	-20...70
Max. relative air humidity	[%]	95
Protection		IP 20

# AC1007



## AS-Interface PLC

Contr 1MSTR 1RS485

### Tests / approvals

Shock/vibration resistance	< 15 g (11ms) / < 55 Hz (0.5mm)
----------------------------	---------------------------------

### AS-i classification

AS-i profile	M1
AS-i certificate	22503

### Mechanical data

Housing	housing for DIN rail mounting
Materials	aluminium

### Displays / operating elements

Display	function check	2 x LED, red
		2 x LED, green
		2 x LED, yellow

### Remarks

Pack quantity	1 pcs.
---------------	--------

### Electrical connection

screw terminals: 5 x

### Connection

