


## Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Please note the changed housing design!



### Product characteristics

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1	
Measuring range	5...240 gph	0.1...4 gpm
Process connection	threaded connection 3/4" NPT	

### Application

Special feature	Gold-plated contacts	
Application	for industrial applications	
Media	Liquids; water; glycol solutions; coolants	
Note on media	oil 1 with viscosity: 10 mm <sup>2</sup> /s (104 °F)	
	oil 2 with viscosity: 46 mm <sup>2</sup> /s (104 °F)	
Medium temperature	[°F]	14...212
Pressure rating	[bar]	40
Pressure rating	[MPa]	4
MAWP (for applications according to CRN)	[bar]	40

### Electrical data

Operating voltage	[V]	18...30 DC; (to SELV/PELV)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes



## Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Power-on delay time	[s]	< 3
---------------------	-----	-----

### Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 2; Number of analogue outputs: 1
------------------------------	---

### Outputs

Total number of outputs	2
Output signal	switching signal; analogue signal; frequency signal; IO-Link; (configurable)
Number of digital outputs	2
Output function	normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC [V]	2
Permanent current rating of switching output DC [mA]	150; (per output 2 x 200 (...140 °F); 2 x 250 (...104 °F))
Switching cycles (mechanical)	10 million
Number of analogue outputs	1
Analogue current output [mA]	4...20
Max. load [Ω]	500
Short-circuit protection	yes
Overload protection	yes
Frequency of the output [Hz]	0...10000

### Measuring/setting range

Measuring range	5...240 gph	0.1...4 gpm
Display range	0...288 gph	0...4.8 gpm
Resolution	1 gph	0.05 gpm
Set point SP	2...240 gph	0.05...4 gpm
Reset point rP	0...238 gph	0...3.95 gpm
Frequency end point, FEP	16...240 gph	0.25...4 gpm
In steps of	1 gph	0.05 gpm
Frequency at the end point FRP [Hz]	10...10000	
Measuring dynamics	1:50	

### Temperature monitoring

Measuring range [°F]	14...212
Display range [°F]	-26...252
Resolution [°F]	2
Set point SP [°F]	16...212
Reset point rP [°F]	14...210
In steps of [°F]	2
Frequency start point, FSP [°F]	14...172
Frequency end point, FEP [°F]	54...212
Frequency at the end point FRP [Hz]	10...10000

### Accuracy / deviations

#### Flow monitoring

Accuracy (in the measuring range)	± (4 % MW + 1 % MEW); (Q > 0,3 l/min; medium and operating temperature: +71,6 °F ± 4K)
-----------------------------------	--



## Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Repeatability	± 1 % MEW	
Temperature monitoring		
Temperature drift	0,9802 °F / K	
Accuracy	[K]	3 K (77 °F; Q > 1 l/min)
Response times		
Flow monitoring		
Response time	[s]	0.01
Damping process value dAP	[s]	0...5
Damping for the analogue output dAA	[s]	0...5
Temperature monitoring		
Dynamic response T05 / T09	[s]	T09 = 120 (Q > 1 l/min)
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; current output; medium selection; damping for the switching output / analogue output; display can be rotated and switched off; standard unit of measurement; process value colour	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor: Process Data Variable; Device Identification	
SIO mode	yes	
Required master port type	A	
Process data analogue	2	
Process data binary	2	
Min. process cycle time	[ms]	5
Supported DeviceIDs	Type of operation	DeviceID
	default	565
Operating conditions		
Ambient temperature	[°F]	32...140
Note on ambient temperature	medium temperature < 176 °F	
	medium temperature < 212 °F: 32...104 °F	
Storage temperature	[°F]	5...176
Protection	IP 65; IP 67	
Tests / approvals		
EMC	DIN EN 61000-6-2	
	DIN EN 61000-6-3	
Shock resistance	DIN EN 60068-2-27	20 g (11 ms)
Vibration resistance	DIN EN 60068-2-6	5 g (10...2000 Hz)
MTTF	[years]	145
UL approval	UL Approval no.	I005
Pressure Equipment Directive	Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	
Mechanical data		
Weight	[g]	696



## Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

Materials	stainless steel (316L/1.4404); PBT+PC-GF30; PBT-GF20; PC; brass chemically nickel-plated
Materials (wetted parts)	stainless steel (316 / 1.4401); stainless steel (316L/1.4404); brass (2.0371); brass chemically nickel-plated; PPS; O-ring: FKM
Process connection	threaded connection 3/4" NPT

### Displays / operating elements

Display	Display unit	3 x LED, green
	switching status	2 x LED, yellow
	measured values	alphanumeric display, red/green 4-digit
	programming	alphanumeric display, 4-digit

### Remarks

Remarks	Recommendation: use a 200-micron filter.
	All data refer to water (68 °F).
	MW = measured value
	MEW = Final value of the measuring range
Notes	Please note the changed housing design!
Pack quantity	1 pcs.

### Electrical connection


Connector: 1 x M12; coding: A; Contacts: gold-plated



## Flow meter with integrated backflow prevention and display

SBN34IQ0FRKG

### Connection



#### OUT1:

- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- frequency output volumetric flow quantity monitoring
- frequency output Temperature monitoring
- IO-Link

#### OUT2:


- switching output volumetric flow quantity monitoring
- switching output Temperature monitoring
- analogue output volumetric flow quantity monitoring
- analogue output Temperature monitoring
- colours to DIN EN 60947-5-2

Core colours :

- BK = black
- BN = brown
- BU = blue
- WH = white

### Diagrams and graphs

#### Pressure loss



dP Pressure loss

Q volumetric flow quantity