




## Evaluation unit for speed monitoring

D100/250VAC

Article no longer available - archive entry



1 mounting on DIN rail



### Product characteristics

Housing	housing for DIN rail mounting
Dimensions [mm]	75 x 55 x 110

### Application

Application	universal evaluation of pulse sequences with regard to overspeed and underspeed; rotational speed monitoring
-------------	--

### Electrical data

Nominal voltage AC [V]	< 250
Nominal voltage DC [V]	24
Nominal voltage tolerance [%]	10
Nominal voltage tolerance 2 [%]	10
Nominal frequency AC [Hz]	50...60
Auxiliary energy for sensors DC [V]	24; ( $\leq 30$ mA)

### Inputs / outputs

Number of inputs and outputs	Number of relay outputs: 1
------------------------------	----------------------------

### Outputs

Number of relay outputs	1
Contact rating	8 A / 1250 VA / 250 V AC

### Measuring/setting range

Setting range [Imp/min]	5...5000
-------------------------	----------

### Accuracy / deviations

Hysteresis [% of Sr]	5...100
Repeatability [% of Sr]	1

# DD0016



## Evaluation unit for speed monitoring

D100/250VAC

Response times		
Start-up delay	[s]	0.5...15
Software / programming		
Adjustment of the switch point		fine adjustment within the range with potentiometer
Operating conditions		
Ambient temperature	[°C]	-20...70
Protection		IP 40
Protection rating terminals		IP 20
Mechanical data		
Housing		housing for DIN rail mounting
Dimensions	[mm]	75 x 55 x 110
Materials		plastics
Displays / operating elements		
Display	switching status	LED, green
	operation	1 x LED, green
Electrical connection		
Connection		

