


Inductive sensor

IEB3001-BPKG/AS-514-TPS

Article no longer available - archive entry

Alternative articles: IE5266

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	1
Housing	threaded type
Dimensions [mm]	M8 x 1

Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	< 9.5
Reverse polarity protection	yes

Outputs

Electrical design	PNP
Output function	normally open
Max. voltage drop switching output DC [V]	1.8
Permanent current rating of switching output DC [mA]	150
Switching frequency DC [Hz]	5000
Short-circuit protection	yes
Type of short-circuit protection	pulsed

**Inductive sensor**

IEB3001-BPKG/AS-514-TPS

Overload protection	yes
---------------------	-----

Detection zone

Sensing range	[mm]	1
Real sensing range S_r	[mm]	$1 \pm 10 \%$
Operating distance	[mm]	0...0.8

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[% of S_r]	1...15
Switch point drift	[% of S_r]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...70
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		threaded type
Mounting		flush mountable
Dimensions	[mm]	M8 x 1
Thread designation		M8 x 1
Materials		brass chromium-plated; PA

Displays / operating elements

Display	switching status	4 x 90° LED, yellow
---------	------------------	---------------------

Accessories

Items supplied	lock nuts: 2
----------------	--------------

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection - plug

Connector: 1 x M8; coding: A



IE5264



Inductive sensor

IEB3001-BPKG/AS-514-TPS

Connection

