




Inductive sensor

IIA3015-BNOG/V4A

Article no longer available - archive entry



Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 81

Electrical data

Operating voltage [V]	10...55 DC
Current consumption [mA]	< 7
Protection class	II
Reverse polarity protection	no

Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	1
Permanent current rating of switching output DC [mA]	400
Switching frequency DC [Hz]	50
Short-circuit protection	no
Overload protection	no

Detection zone

Sensing range [mm]	15
Real sensing range S_r [mm]	$15 \pm 10 \%$
Operating distance [mm]	0...12.1

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis [% of S_r]	3...15
Switch point drift [% of S_r]	-10...10


II5104



Inductive sensor

IIA3015-BNOG/V4A

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5 / L = 81
Thread designation		M30 x 1.5
Materials		stainless steel (316Ti/1.4571); sensing face: PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.5 mm²		
Connection		



BK = Core colours :
BN = black
BU = brown
blue