


# KQ1001



## Continuous level sensor

KQ-5xxxNFPKG/IO/0,1M/US



Product characteristics	
Electrical design	PNP/NPN; (parameterisable)
Communication interface	IO-Link
Housing	rectangular
Dimensions [mm]	255 x 28 x 16.7
Application	
Application	Continuous level measurement behind non-metallic and non-conductive surfaces
Media	dry bulk material; aqueous solutions; oils
Cannot be used for	highly adhesive media

# KQ1001



## Continuous level sensor

KQ-5xxxNFPKG/IO/0,1M/US

Electrical data		
Operating voltage	[V]	10...30 DC; (IO-Link: 18...30 DC)
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	1300
Measuring principle		capacitive
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 3
Outputs		
Electrical design		PNP/NPN; (parameterisable)
Number of digital outputs		3
Permanent current rating of switching output DC	[mA]	200
Max. resistance switching output	[Ω]	8
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Measuring range	[mm]	< 200
Measuring/setting range		
Detection range	[mm]	228
Set point SP	[%]	5...95
Reset point rP	[%]	4...94
In steps of	[%]	1
Accuracy / deviations		
Repeatability		2
	[% of the final value]	
Offset deviation		4
	[% of the final value]	
Resolution		1
	[% of the final value]	
Linearity deviation		1
	[% of the final value]	
Response times		
Response time	[ms]	1300
Software / programming		
Parameter setting options		Damping; hysteresis / window; fault indication; diagnostic function; sensitivity; internal temperature; limitation of measuring range; Adjustable switching delay; zero-point calibration; direction of installation; LEDs can be deactivated
Interfaces		
Communication interface		IO-Link
Transmission type		COM2 (38,4 kBaud)
IO-Link revision		1.1

# KQ1001



## Continuous level sensor

KQ-5xxxNFPKG/IO/0,1M/US

SDCI standard	IEC 61131-9	
Profiles	Smart Sensor - SSP 3.1	Measuring Sensor
	Common - I&D	Identification and Diagnosis
SIO mode	yes	
Required master port type	A	
Process data analogue	1	
Process data binary	3	
Min. process cycle time [ms]	7.2	
IO-Link process data (cyclical)	<b>function</b>	<b>bit length</b>
	process value	16
	exponent	8
	device status	4
	binary switching information	3
IO-Link functions (acyclical)	direction of installation; limitation of sensor elements; sensitivity; minimum recognition threshold; Performance in case of a fault; error delay; Damping; LED mode; switch-on cycle counter; operating hours counter; switching cycles counter; min./max. process value; internal temperature; min./max. internal temperature; diagnostic data for level	
Supported DeviceIDs	<b>Type of operation</b>	<b>DeviceID</b>
	default	924
Note	For further information please see the IODD PDF file under "Downloads"	

Operating conditions		
Applications	DIN EN 60654-1 application class B2	
Ambient temperature [°C]	-20...80	
Storage temperature [°C]	-25...85	
Protection	IP 65	

Tests / approvals		
EMC	DIN EN 61000-6-4 30 - 230 MHz	40 dB $\mu$ V/m QP / 10 m distance
	230 - 1 GHz	47 dB $\mu$ V/m QP / 10 m distance
	DIN EN 61000-4-2	$\pm$ 25 kV AD / $\pm$ 25 kV CD
	DIN EN 61000-4-3	80 MHz - / 1 GHz 10 V/m
	DIN EN 61000-4-4	$\pm$ 2.5 kV / 5 kHz
		$\pm$ 2.5 kV / 100 kHz
	DIN EN 61000-4-6	10 V
Shock resistance	EN 60068-2-27	15 g 11 ms
Vibration resistance	EN 60068-2-6	5 g (10...2000 Hz)
MTTF [years]	290.43	
UL approval	Ta	-25...60 °C
	Enclosure type	Type 1
	power supply	Limited Voltage/Current
	UL approval no.	D006
	File number UL	E174191

Mechanical data		
Weight [g]	377.5	
Housing	rectangular	
Dimensions [mm]	255 x 28 x 16.7	
Materials	PBT; PC;	

# KQ1001



## Continuous level sensor

KQ-5xxxNFPKG/IO/0,1M/US

### Displays / operating elements

Display	operation	1 x LED, green
	switching status	3 x LED, yellow
	function	20 x LED, green

### Accessories


Items supplied	adhesive tape: 1 x (1,2 x 23 x 240 mm)
Accessories (optional)	Mounting adapter: 2, E12675
	Mounting adapter: 2, E12676
	Fixing strap: 5, E10880
	adhesive tape: 10, E12677

### Remarks


Remarks	when used on IO-Link class B masters switching outputs OUT2, OUT3 have to be switched off
Pack quantity	1 pcs.

### Electrical connection

Connector: 1 x M12; coding: A; Contacts: 5



### Connection



### Electrical connection - plug

Cable: 0.1 m, PUR