


## Through-beam sensor receiver

OGE-DPKG/US



### Product characteristics

Type of light	red light
Housing	threaded type

### Application

Function principle	Through-beam sensor
--------------------	---------------------

### Electrical data

Operating voltage [V]	10...30 DC
Current consumption [mA]	8
Protection class	III
Reverse polarity protection	yes
Type of light	red light
Wave length [nm]	645

### Outputs

Electrical design	PNP
Output function	dark-on mode
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	1000
Short-circuit protection	yes
Overload protection	yes

### Detection zone

Transmitter / receiver	receiver
Range [m]	< 8
Range adjustable	no

### Operating conditions

Ambient temperature [°C]	-25...60
Protection	IP 67; (in conjunction with a corresponding connector)



## Through-beam sensor receiver

OGE-DPKG/US

Tests / approvals		
EMC	EN 60947-5-2	
MTTF	[years]	1335
Mechanical data		
Weight	[g]	14.7
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 44
Thread designation		M18 x 1
Materials		housing: ABS
Lens material		PMMA
Displays / operating elements		
Display	switching status	1 x LED, yellow
Accessories		
Items supplied		lock nuts: 2
Remarks		
Pack quantity		1 pcs.
Electrical connection		

Connector: 1 x M12; coding: A



### Connection

