
PV7600

Pressure switch with IO-Link

PV-400-SEN14-UFRVG/US/ /



Product characteristics				
Number of inputs and outputs		Number of digital outputs: 2		
Measuring range		0...400 bar	0...5800 psi	0...40 MPa
Process connection		threaded connection 1/4" NPT external thread internal thread:M5		
Application				
Measuring element		metallic thin film cell		
Application		for industrial applications		
Media		liquids and gases		
Medium temperature	[°C]	-40...90		
Min. bursting pressure		1700 bar	24655 psi	170 MPa
Pressure rating		1000 bar	14500 psi	100 MPa
Note on pressure rating		static		
Vacuum resistance	[mbar]	-1000		
Type of pressure		relative pressure		
MAWP (for applications according to CRN)	[bar]	840		
Electrical data				
Operating voltage	[V]	18...30 DC		
Current consumption	[mA]	< 15		
Min. insulation resistance	[MΩ]	100; (500 V DC)		
Protection class		III		
Reverse polarity protection		yes		
Power-on delay time	[s]	< 0.3		
Inputs / outputs				
Number of inputs and outputs		Number of digital outputs: 2		
Outputs				
Total number of outputs		2		

PV7600

Pressure switch with IO-Link

PV-400-SEN14-UFRVG/US/ /

Output signal	switching signal; IO-Link; (configurable)	
Electrical design	PNP/NPN	
Number of digital outputs	2	
Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]	2	
Permanent current rating of switching output DC [mA]	100	
Switching frequency DC [Hz]	< 170	
Short-circuit protection	yes	
Type of short-circuit protection	pulsed	
Overload protection	yes	
Measuring/setting range		
Measuring range	0...400 bar	0...5800 psi / 0...40 MPa
Set point SP	4...400 bar	58...5802 psi / 0.4...40 MPa
Reset point rP	2...398 bar	30...5773 psi / 0.2...39.8 MPa
In steps of	0.2 bar	1 psi / 0.02 MPa
Factory setting	SP1 = 100 bar; rP1 = 92 bar; ou1 = Hno;	
	SP2 = 300 bar; rP2 = 292 bar; ou2 = Hno;	
	dS1/dS2 = 0 ms; dr1/dr2 = 0 ms	
	coF = 0 %; P-n = PnP; dAP= 60 ms	
Accuracy / deviations		
Switch point accuracy [% of the span]	< ± 0,5 (nach DIN EN 61298-2)	
Repeatability [% of the span]	< ± 0,05; (with temperature fluctuations < 10 K)	
Characteristics deviation [% of the span]	< ± 0,5; (linearity incl. hysteresis and repeatability, limit value setting to DIN EN IEC 62828-1)	
Linearity deviation [% of the span]	< ± 0,1 (BFSL) / < ± 0,2 (LS)	
Hysteresis deviation [% of the span]	< ± 0,2	
Long-term stability [% of the span]	< ± 0,1; (per 6 months)	
Temperature coefficient zero point [% of the span / 10 K]	< 0,1 (-25...90 °C) / < 0,2 (-40...-25 °C)	
Temperature coefficient span [% of the span / 10 K]	< 0,1 (-25...90 °C) / < 0,2 (-40...-25 °C)	
Response times		
Response time [ms]	< 3	
Software / programming		
Parameter setting options	hysteresis / window; normally open / normally closed; switching logic; switch-on/switch-off delay; Damping	
Interfaces		
Communication interface	IO-Link	
Transmission type	COM2 (38,4 kBaud)	

PV7600

Pressure switch with IO-Link

PV-400-SEN14-UFRVG/US/ /

IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor: Process Data Variable; Device Identification, Device Diagnosis	
SIO mode		yes	
Required master port type		A	
Process data analogue		2	
Process data binary		2	
Min. process cycle time	[ms]	5	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	851

Operating conditions			
Ambient temperature	[°C]	-40...90	
Storage temperature	[°C]	-40...100	
Protection		IP 67; IP 69K	


Tests / approvals			
EMC		DIN EN 61326-1	
Shock resistance		DIN EN 60068-2-27	500 g (1 ms)
Vibration resistance		DIN EN 60068-2-6	20 g (10...2000 Hz)
MTTF	[years]	668	
UL approval		UL Approval no.	J016
Pressure Equipment Directive		Sound engineering practice; can be used for group 2 fluids; group 1 fluids on request	

Mechanical data		
Weight	[g]	65
Materials		1.4542 (17-4 PH / 630); stainless steel (1.4404 / 316L); PEI
Materials (wetted parts)		stainless steel (1.4305 / 303); 1.4542 (17-4 PH / 630)
Min. pressure cycles		60 million; (at 1.2 times nominal pressure)
Tightening torque	[Nm]	50; (recommended tightening torque; depends on lubrication, seal and pressure rating)
Process connection		threaded connection 1/4" NPT external thread internal thread:M5
Restrictor element integrated		yes

Remarks	
Remarks	BFSL = Best Fit Straight Line
	LS = limit value setting
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A




PV7600

Pressure switch with IO-Link

PV-400-SEN14-UFRVG/US/ /

Connection



OUT1	switching output IO-Link
OUT2	switching output
	colours to DIN EN 60947-5-2
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white