


# SF3214



## Flow sensor for connection to an evaluation unit

SFR12ABBE0/40M

Article no longer available - archive entry



### Product characteristics

Process connection G 1/2 external thread

### Application

Application Ex zone 0  
 Medium temperature [°C] -20...60  
 Pressure rating [bar] 30

### Liquids

Application Ex zone 0  
 Medium temperature [°C] -20...60

### Gases

Medium temperature [°C] -20...60

### Electrical data

Connection to control monitor VS 0200 Exi

### Measuring/setting range

#### Liquids

Setting range [cm/s] 3...300  
 Greatest sensitivity [cm/s] 3...60

#### Gases

Setting range [cm/s] 200...2000  
 Greatest sensitivity [cm/s] 200...800

### Accuracy / deviations

Temperature gradient [K/min] 15

### Response times

Response time [s] 1...10

#### Liquids

Response time [s] 1...10

#### Gases

Response time [s] 1...10

### Operating conditions

Protection IP 67

# SF3214



## Flow sensor for connection to an evaluation unit


SFR12ABBE0/40M

Mechanical data	
Housing	threaded type
Materials	stainless steel (1.4571/316Ti)
Materials (wetted parts)	stainless steel (1.4571/316Ti)
Process connection	G 1/2 external thread

Remarks	
Pack quantity	1 pcs.

**Electrical connection**  
Cable: 40 m, TPE-S; Maximum cable length: 100 m; 5 x 0.34 mm<sup>2</sup>

### Connection



	Core colours :
BN =	brown
BU =	blue
BK =	black
WH =	white
GY =	grey