




Flow monitor

SCR14ABAFPKG/US-100-IPF

Article no longer available - archive entry

Alternative articles: SI5000 + E40099
When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics	
Number of inputs and outputs	Number of digital outputs: 1
Process connection	G 1/4 external thread
Application	
Media	Liquids
Medium temperature [°C]	-25...80
Pressure rating [bar]	30
Electrical data	
Operating voltage [V]	20...36 DC
Current consumption [mA]	< 45
Reverse polarity protection	yes
Power-on delay time [s]	< 20
Inputs / outputs	
Number of inputs and outputs	Number of digital outputs: 1
Outputs	
Total number of outputs	1
Output signal	switching signal
Electrical design	PNP
Number of digital outputs	1



Flow monitor

SCR14ABAFPKG/US-100-IPF

Output function	normally open / normally closed; (parameterisable)	
Max. voltage drop switching output DC [V]		2.5
Permanent current rating of switching output DC [mA]		400
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Measuring/setting range

Setting range [cm/s]		3...300
Greatest sensitivity [cm/s]		3...60

Accuracy / deviations

Temperature gradient [K/min]		15
------------------------------	--	----

Response times

Response time [s]		1...10
-------------------	--	--------

Software / programming

Adjustment of the switch point		potentiometer
--------------------------------	--	---------------

Operating conditions

Ambient temperature [°C]		-20...80
Protection		IP 67

Mechanical data

Materials		PBT-GF20
Materials (wetted parts)		stainless steel (1.4305 / 303)
Process connection		G 1/4 external thread

Displays / operating elements

Display	function	11 x LED
---------	----------	----------

Accessories

Items supplied		sealings: 2 x AMF 30
		screwdrivers

Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Connector: 1 x M12; coding: A




ST2604



Flow monitor

SCR14ABAFPKG/US-100-IPF

Connection



BN = Core colours :
BU = brown
BK = blue
black