

QHA200



Hardware for operating moneo in the production environment


moneo appliance

Article no longer available - archive entry

Alternative articles: QHA210

When selecting an alternative article and accessories please note that technical data may differ!

licences required for the operation of moneo products have to be ordered separately



- 1 power supply
- 2 audio
- 3 microphone input
- 4 COM interface x 2
- 5 VGA interface
- 6 DisplayPort interface
- 7 HDMI interface
- 8 USB interface x 4
- 9 Ethernet interface 2
- 10 Ethernet interface 1





Hardware for operating moneo in the production environment

moneo appliance

Application		
Application	IT hardware for operation of moneo	
	providing memory capacity and processing power	
	moneo software preinstalled	
	Easy set-up without requiring special IT knowledge	
Content description	incl. management system for appliance maintenance	
Compatibility	can be used independent of IT infrastructure	
	can be integrated in IT network structure at any time	
Connectivity	interfaces for sensor and IT network	
Maintenance and support	integrated update, back-up and support functions via Appliance Management System	
Electrical data		
Operating voltage	[V]	12...24 DC
Current consumption	[mA]	2200; (24 V)
Outputs		
Number of video outputs	3; (DP: 1x; HDMI: 1x; VGA: 1x)	
Software / programming		
Language	English	
Included licences	appliance management system (AMS)	
Note on licence	hardware bound; licences required for the operation of moneo products have to be ordered separately	
Operating system	Debian Linux 10	
System requirements		
Web browser	Google Chrome; Mozilla Firefox; (supported versions: see current release notes)	
Interfaces		
Communication interface	Ethernet; RS232; USB	
Number of Ethernet interfaces	2; (GBit)	
Number of R232 interfaces	2; (selectable via BIOS: RS232 / RS485)	
Number of USB interfaces	4; (USB 3.0)	
Operating conditions		
Ambient temperature	[°C]	-20...50
Storage temperature	[°C]	-40...85
Max. relative air humidity	[%]	95; (40 °C non condensing)
Protection	IP 67; (lower part: IP 21)	
Tests / approvals		
Shock resistance	IEC60068-2-27	50 g 11 ms
Vibration resistance	IEC 60068-2-6	5 Grms / 10...500 Hz
Mechanical data		
Weight	[g]	5653
Dimensions	[mm]	85 x 253 x 201
Hardware		
Chip set	Intel Q170	
Processor	Intel Core i5 6500TE Quadcore 2,3 GHz	
TPM chip	V 2.0	

QHA200



Hardware for operating moneo in the production environment

moneo appliance

BIOS	AMI EFI BIOS
Working memory	8 GB DDR3
Mass storage	128 GB SSD

Remarks

Notes	licences required for the operation of moneo products have to be ordered separately
Pack quantity	1 pcs.