




## Capacitive sensor

KG-3002-BNKG/NI

Article no longer available - archive entry

Alternative articles: KG5046

When selecting an alternative article and accessories please note that technical data may differ!



### Product characteristics

Electrical design	NPN
Output function	normally closed
Sensing range [mm]	1.6; (fixed, sealed with screw retaining compound)
Housing	threaded type
Dimensions [mm]	M18 x 1 / L = 84

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 10 (24 V DC) / < 15 (36 V DC)
Protection class	II
Reverse polarity protection	yes

### Outputs

Electrical design	NPN
Output function	normally closed
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	250
Switching frequency DC [Hz]	50
Short-circuit protection	yes
Type of short-circuit protection	pulsed
Overload protection	yes

### Detection zone

Sensing range [mm]	1.6; (fixed, sealed with screw retaining compound)
Real sensing range Sr [mm]	1.6; ( $\pm 0,1$ )

### Accuracy / deviations

Correction factor	glass: 0.4 / water: 1 / ceramics: 0.2 / PVC: 0.2
Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-15...15


# KG5055



## Capacitive sensor

KG-3002-BNKG/NI

Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Increased immunity		yes
Tests / approvals		
EMC	EN 60947-5-2	
Mechanical data		
Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M18 x 1 / L = 84
Thread designation		M18 x 1
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, yellow
Remarks		
Pack quantity		1 pcs.
Electrical connection		
Cable: 2 m, PVC; 3 x 0.34 mm <sup>2</sup>		
Connection		



BN = Core colours : brown  
BU = blue  
BK = black