


Fibre optic through-beam sensor

FE-30-A-A-M6/4M

Article no longer available - archive entry



Application

Function principle	Through-beam sensor
--------------------	---------------------

Detection zone

Range with fibre-optic amplifier type	OIF
---------------------------------------	-----

OIF

Range of fibre optics [mm]	154
----------------------------	-----

Operating conditions

Ambient temperature [°C]	-40...290
--------------------------	-----------

Mechanical data

Version of sensing head	straight
Sensing head thread	M6
Total length [mm]	4000
Min. bending radius [mm]	30
Materials	Adapter: PA
Fibre material	glass
Fibre head material	aluminium
Fibre sheath material	aluminium

E20308



Fibre optic through-beam sensor

FE-30-A-A-M6/4M

Remarks	
---------	--

Pack quantity	1 pcs.
---------------	--------