




Object inspection sensor

O2VIRPKG/O/V/GM/E1/E2/W

For 8-pole sockets the core colours are not standardised.
Please note the wiring of the sensor and the sockets (see data sheet).



- 1 Display
2 focus adjustment screw
3 centre of the lens axes



Product characteristics

Type of light		infrared light
Image resolution	[px]	640 x 480
Max. reading rate	[Hz]	20

Electrical data

Operating voltage tolerance	[%]	10
Operating voltage	[V]	24 DC
Current consumption	[mA]	300
Protection class		III
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	850
Image sensor		CMOS image sensor black/white

Inputs / outputs

Number of inputs and outputs	Number of digital inputs: 2; Number of digital outputs: 5
------------------------------	---

Inputs

Trigger	24 V PNP (IEC 61131-2 Typ 1); internal
Number of digital inputs	2



Object inspection sensor

O2VIRPKG/O/V/GM/E1/E2/W

Input circuit of digital inputs		24 V PNP; (configurable; IEC 61131-2 Typ 1)			
Outputs					
Total number of outputs		5			
Number of digital outputs		5; (configurable)			
Output function		24 V PNP			
Max. voltage drop switching output DC [V]		2			
Max. current load per output [mA]		100			
Short-circuit protection		yes			
Overload protection		yes			
Detection zone					
Field of view size [mm]	Operating distance	field of view	Smallest detectable object	Resolution	
	50	33 x 24	0,3	0,075	
	75	50 x 36	0,4	0,1	
	100	66 x 47	0,5	0,125	
	200	132 x 94	0,9	0,225	
	400	264 x 189	1,7	0,425	
	1000	660 x 472	4,0	1,0	
	2000	1320 x 945	8,0	2,0	
Image resolution [px]	640 x 480				
Max. reading rate [Hz]	20				
Software / programming					
Parameter setting options		via two pushbuttons and 10-segment display or via PC / notebook with operating software			
Interfaces					
Communication interface		Ethernet			
Ethernet					
Number of Ethernet interfaces		1			
Transmission standard		10Base-T; 100Base-TX			
Transmission rate		10; 100			
Protocol		TCP/IP; EtherNet/IP			
Factory settings		IP address: 192.168.0.59			
		subnet mask: 255.255.255.0			
		gateway IP address: 192.168.0.201			
		MAC address: see type label			
Operating conditions					
Ambient temperature [°C]	-10...60				
Storage temperature [°C]	-40...85				
Protection	IP 67				
Tests / approvals					
EMC	radiation of interference	EN 61326			
	immunity	EN 61326			
Shock resistance	EN 60947-5-2, 7.4.1				
	IEC 60068-2-27				



Object inspection sensor

O2VIRPKG/O/V/GM/E1/E2/W

Vibration resistance	EN 60947-5-2, 7.4.2	
	IEC 60028-2-6	

Mechanical data

Weight	[g]	434
Dimensions	[mm]	60 x 42 x 53.5
Materials	housing: diecast zinc powder-coated; front pane: glass; LED window: PC	

Displays / operating elements

Display	function	3 x LED, green
	switching status	4 x LED, yellow
		10-segment display, 4-digit

Accessories

Accessories (optional)	Operating software
	Mounting accessories

Remarks

Remarks	operating voltage "supply class 2" according to cULus
Pack quantity	1 pcs.

Electrical connection - Ethernet

Connector: 1 x M12; coding: D



1	TD+
2	RD+
3	TD-
4	RD-

Electrical connection - Process connection

Connector: 1 x M12; coding: A



1	U+
2	trigger input
3	0 V
4	switching output 5 / trigger output
5	switching output 3 / Ready
6	switching output 4 / OUT
7	switching output 1 / input 1
8	switching output 2 / input 2