
LMT03A

Sensor for point level detection in hazardous areas

LMDCE-A12E-QSKG-1/US/3D/3G



1 Tightening torque 20...25 Nm

CE EC 1935/2004 EHEDG Tested Ex FDA IO-Link UKCA

Product characteristics		
Number of inputs and outputs		Number of digital outputs: 2
Factory setting		oils; oil-based media; powder
Process connection		threaded connection G 1/2 sealing cone
Application		
Special feature		Gold-plated contacts
Media		Liquids; viscous media; powder
Cannot be used for		See the operating instructions, chapter "Function and features".
Medium temperature	[°C]	-20...85
Probe length	[mm]	153
Tank pressure	[bar]	-1...40
Electrical data		
Operating voltage	[V]	18...30 DC
Current consumption	[mA]	< 50
Protection class		III
Reverse polarity protection		yes
Measuring principle		capacitive
Inputs / outputs		
Number of inputs and outputs		Number of digital outputs: 2
Outputs		
Total number of outputs		2
Output signal		switching signal; IO-Link
Electrical design		PNP/NPN
Number of digital outputs		2
Output function		normally open / normally closed; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5

LMT03A

Sensor for point level detection in hazardous areas

LMDCE-A12E-QSKG-1/US/3D/3G

Permanent current rating of switching output DC	[mA]	100	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Measuring/setting range			
Factory setting		oils; oil-based media; powder	
Response times			
Response time	[s]	< 0.5	
Interfaces			
Communication interface		IO-Link	
Transmission type		COM2 (38,4 kBaud)	
IO-Link revision		1.1	
SDCI standard		IEC 61131-9	
Profiles		Smart Sensor: Process Data Variable; Device Identification	
SIO mode		yes	
Required master port type		A	
Process data analogue		1	
Process data binary		2	
Min. process cycle time	[ms]	2.3	
Supported DeviceIDs		**Type of operation**	**DeviceID**
		default	642
Operating conditions			
Ambient temperature	[°C]	-20...60	
Storage temperature	[°C]	-40...85	
Protection		IP 67; (when used outside the hazardous area: IP 68 / IP 69)	
Tests / approvals			
ATEX marking		II 3D Ex tc IIIC T90°C Dc X	
		II 3G Ex nA IIC T4 Gc X	
EMC		DIN EN 61000-6-2	
		DIN EN 61000-6-4	closed tanks
Shock resistance		DIN EN 60068-2-27	50 g (11 ms)
Vibration resistance		DIN EN 60068-2-6	8 g (10...2000 Hz)
MTTF	[years]	222	
Mechanical data			
Weight	[g]	329	
Materials		stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti); PEEK; PEI; FKM	
Materials (wetted parts)		stainless steel (1.4404 / 316L); stainless steel (1.4571/316Ti); PEEK; surface characteristics: Ra < 0,8 / Rz 4; FKM	
Process connection		threaded connection G 1/2 sealing cone	
Displays / operating elements			
Display		switching status	LED, yellow
		operating status	LED, green

LMT03A

Sensor for point level detection in hazardous areas

LMDCE-A12E-QSKG-1/US/3D/3G


Remarks	
Pack quantity	1 pcs.

Electrical connection

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection



OUT1:	switching output IO-Link Teach
OUT2:	switching output
	colours to DIN EN 60947-5-2
	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white