
ST2000

Flow sensor for connection to an evaluation unit

STR14ABA

Article no longer available - archive entry



Product characteristics		
Process connection		G 1/4 external thread
Application		
Application		high-temperature range
Media		Liquids; Gases
Medium temperature	[°C]	-25...80
Pressure rating	[bar]	30
Liquids		
Application		high-temperature range
Medium temperature	[°C]	-25...80
Gases		
Medium temperature	[°C]	-25...80
Electrical data		
Connection to control monitor		VS 0100
Measuring/setting range		
Liquids		
Setting range	[cm/s]	3...300
Greatest sensitivity	[cm/s]	3...60
Gases		
Setting range	[cm/s]	5...1500
Accuracy / deviations		
Temperature gradient	[K/min]	15
Response times		
Response time	[s]	1...10
Liquids		
Response time	[s]	1...10
Gases		
Response time	[s]	1...10
Operating conditions		
Protection		IP 67

ST2000

Flow sensor for connection to an evaluation unit

STR14ABA


Mechanical data	
Housing	threaded type
Materials	stainless steel (1.4305 / 303)
Process connection	G 1/4 external thread

Remarks	
Pack quantity	1 pcs.

Electrical connection

Cable: 2 m, Silflex-PUR; Maximum cable length: 100 m; 4 x 0.5 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white