


E11844



Connecting cable with socket

ADOAH050MSN0050A05

Article no longer available - archive entry




| Application | |
|---|---|
| Application | Ex zone 1 |
| Electrical data | |
| Operating voltage [V] | 10...30 DC |
| Operating conditions | |
| Ambient temperature [°C] | -25...90 |
| Protection | IP 67 |
| Safety classification | |
| Max. internal capacitance [nF] | 3.8 |
| Max. internal inductance [µH] | 29.5 |
| Mechanical data | |
| Dimensions [mm] | 27 x 15 x 39 |
| Materials | TPU |
| Material nut | brass, nickel-plated |
| Remarks | |
| Remarks | When using sockets in hazardous areas (ATEX) there are special requirements regarding wiring. The requirements of the applicable installation regulations must be absolutely adhered to by the user on his own responsibility. |
| Pack quantity | 1 pcs. |
| Electrical connection | |
| Cable: 50 m, PUR / PVC, blue, Ø 6 mm; 5 x 0.34 mm ² (42 x Ø 0.1 mm) | |
| Electrical connection - socket | |
| Connector: 1 x M12, angled; Moulded body: TPU; Locking: brass, nickel-plated | |

E11844



Connecting cable with socket

ADOAH050MSN0050A05



Connection

| | |
|---|----|
| 1 | BN |
| 2 | WH |
| 3 | BU |
| 4 | BK |
| 5 | GY |

Core colours :

| | |
|------|-------|
| BK = | black |
| BN = | brown |
| BU = | blue |
| GY = | grey |
| WH = | white |

Article no longer available - archive entry