


# IO5008



## Inductive sensor

IOC2010-ARKG/2M/PUR/FRONT

Article no longer available - archive entry



- 1 mounting holes M4 reinforced  
2 Sensing face



### Product characteristics

Electrical design		PNP/NPN
Output function		normally open
Sensing range	[mm]	10
Housing		rectangular
Dimensions	[mm]	26 x 26 x 42

### Electrical data

Operating voltage	[V]	10...55 DC
Protection class		II
Reverse polarity protection		yes

# IO5008



## Inductive sensor

IOC2010-ARKG/2M/PUR/FRONT

Outputs		
Electrical design		PNP/NPN
Output function		normally open
Max. voltage drop switching output DC	[V]	4.5
Minimum load current	[mA]	2
Max. leakage current	[mA]	0.6
Permanent current rating of switching output DC	[mA]	100
Switching frequency DC	[Hz]	250
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes
Detection zone		
Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1
Accuracy / deviations		
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10
Operating conditions		
Ambient temperature	[°C]	-25...80
Protection		IP 67
Tests / approvals		
EMC	EN 60947-5-2 EN 55011	class B
Mechanical data		
Housing		rectangular
Sensing face		front
Mounting		flush mountable
Dimensions	[mm]	26 x 26 x 42
Materials		PBT
Displays / operating elements		
Display	switching status	1 x LED, red
Remarks		
Pack quantity		1 pcs.

# IO5008





## Inductive sensor

IOC2010-ARKG/2M/PUR/FRONT

### Electrical connection

Cable: 2 m, PUR; 2 x 0.5 mm<sup>2</sup>

### Connection



Core colours :

BN = brown  
BU = blue

Article no longer available - archive entry