

# IG5887




## Inductive sensor

IGA3005-BPKG/2,5M/T RT

discontinued article

replaced by: IG5397; discontinued article – Discontinuation date: 31.03.2018



### Electrical data

Operating voltage	[V]	10...36 DC
Current consumption	[mA]	15; (24 V)
Protection class		II
Reverse polarity protection		yes

### Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	250
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

### Detection zone

Sensing range	[mm]	5
Real sensing range $S_r$	[mm]	$5 \pm 10\%$
Operating distance	[mm]	0...4.05

# IG5887



## Inductive sensor

IGA3005-BPKG/2,5M/T RT

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.5 / aluminium: 0.4 / copper: 0.3	
Hysteresis [% of Sr]	3...15	
Switch point drift [% of Sr]	-10...10	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
MTTF [years]	2444	
Mechanical data		
Weight [g]	236.5	
Housing	threaded type	
Mounting	flush mountable	
Dimensions [mm]	M18 x 1	
Thread designation	M18 x 1	
Materials	brass white bronze coated; PBT	
Displays / operating elements		
Display	switching status	1 x LED, red
Accessories		
Accessories (supplied)	lock nuts: 2	
Remarks		
Notes	discontinued article	
Pack quantity	1 pcs.	

# IG5887



## Inductive sensor

IGA3005-BPKG/2,5M/T RT

### Electrical connection

Cable: 2.5 m, PTFE; 3 x 0.75 mm<sup>2</sup>

### Connection



Core colours :

BK = black  
BN = brown  
BU = blue

discontinued article

replaced by: IG5397; discontinued article – Discontinuation date: 31.03.2018