


ST2300



Flow sensor for connection to an evaluation unit

STR14ZBB

Article no longer available - archive entry



Product characteristics

Process connection	G 1/4 external thread
--------------------	-----------------------

Application

Application	high-temperature range
Media	Liquids; Gases
Pressure rating [bar]	30

Liquids

Application	high-temperature range
Medium temperature [°C]	0...120

Gases

Medium temperature [°C]	0...100
-------------------------	---------

Electrical data

Connection to control monitor	VS 0100
-------------------------------	---------

Measuring/setting range

Liquids

Setting range [cm/s]	3...300
Greatest sensitivity [cm/s]	3...60

Gases

Setting range [cm/s]	5...1500
----------------------	----------

Accuracy / deviations

Temperature gradient [K/min]	15
------------------------------	----

Response times

Response time [s]	1...10
-------------------	--------

Liquids

Response time [s]	1...10
-------------------	--------

Gases

Response time [s]	1...10
-------------------	--------

Operating conditions

Protection	IP 67
------------	-------

Mechanical data

Housing	threaded type
---------	---------------

ST2300



Flow sensor for connection to an evaluation unit

STR14ZBB

Materials	stainless steel (1.4571/316Ti)
Process connection	G 1/4 external thread


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 2 m, silicone; Maximum cable length: 100 m; 4 x 0.5 mm²

Connection



	Core colours :
BK =	black
BN =	brown
BU =	blue
WH =	white