




AS-Interface universal module

EMS/Module/4DI/CCT

Article no longer available - archive entry



1 panel for labelling



Electrical data		
Operating voltage	[V]	26.5...31.6 DC
Current consumption	[mA]	< 50
Inputs / outputs		
Number of inputs and outputs	Number of digital inputs: 4	
Inputs		
Number of digital inputs	4	
Sensor supply of the inputs	AS-i	
Input current High	[mA]	3...5
Input current Low	[mA]	0.5...1
Outputs		
Electrical design	AS-i	
Operating conditions		
Ambient temperature	[°C]	-25...60
Protection	IP 65	
Tests / approvals		
EMC	EN 50295	
AS-i classification		
AS-i profile	S-0.F	
AS-i I/O configuration	[hex]	0
AS-i ID code	[hex]	F



AS-Interface universal module

EMS/Module/4DI/CCT

Assignment of the data bits	data bit		D0	D1	D2	D3
	assignment		I-1	I-2 /	I-3	I-4
Assignment of the parameter bits	parameter bit	function				
	P0	sensor monitoring	: I1	deactivated	* /	activated
	P1	sensor monitoring	: I2	deactivated	* /	activated
	P2	sensor monitoring	: I3	deactivated	* /	activated
	P3	sensor monitoring	: I4	deactivated	* /	activated

Mechanical data

Type of mounting	AS-i interface to FC and SC lower parts
Materials	PA 6-GF30; stainless steel (1.4305 / 303)

Displays / operating elements

Display	operation	LED, green
	function	LED, yellow

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

cage clamps:

contact pins to module lower part, FK / PG: