


IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP69K



Electrical data

Operating voltage	[V]	18...30 DC; (US)
Current consumption	[mA]	50; (US)
Protection class		III
Additional voltage supply	[V]	18...28 DC; (UA)
Max. current consumption from additional supply	[mA]	3600; (UA)

Inputs / outputs

Number of inputs and outputs	Number of digital outputs: 20
------------------------------	-------------------------------



IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP69K

Outputs		
Number of digital outputs	20; (10 x 2)	
Circuit	PNP	
Output function	transistor	
Max. current load per output [mA]	1800	
Max. current load outputs total [A]	3.6; (Max. current load per output side: 1800 mA)	
Electrically separated	yes	
Interfaces		
Communication interface	IO-Link	
Supported DeviceIDs	Type of operation	DeviceID
	default	996
IO-Link Device		
Transmission type	COM2 (38,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9	
SIO mode	no	
Min. process cycle time [ms]	5.6	
Operating conditions		
Ambient temperature [°C]	-25...60	
Storage temperature [°C]	-25...70	
Max. relative air humidity [%]	90	
Max. height above sea level [m]	2000	
Protection	IP 65; IP 67; IP 69K; (operation with stainless steel protective caps: IP 69K)	
Protection rating (NEMA 250)	6P	
Pollution degree	2	
Chemical media	ISO 16750-5	HLP, CC, DB, DC, DD, CA
	NEMA 250 5.13.1	AA
Tests / approvals		
EMC	EN 61000-6-2	
	EN 61000-6-3	
	IEC 61131-9	
Shock resistance	DIN EN 60068-2-27	
Vibration resistance	DIN EN 60068-2-64	
	DIN EN 60068-2-6	
MTTF [years]	41	
Mechanical data		
Weight [g]	422.8	
Dimensions [mm]	26 x 59.3 x 208	
Materials	housing: PA grey; socket: stainless steel (316L/1.4404)	
Sealing material	EPDM	
Displays / operating elements		
Display	operation	LED, green
	errors	LED, red
	function	LED, yellow



IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP69K

Accessories

Accessories (optional)

Protective caps M12

Remarks

Pack quantity

1 pcs.

Electrical connection - IO-Link

Connector: M12; coding: A




X1

1	+ 24 V DC (US)
2	not used
3	GND (US)
4	IO-Link

Electrical connection - Outputs

Connector: M12; coding: A; Sealing: EPDM



X1.0...X1.9

1	not used
2	DO2
3	GND (UA)
4	DO1
5	not used

Electrical connection - power supply

Connector: M12; coding: A



AL2231



IO-Link CompactLine module

IO-Link Module 10x2 DO M12 IP69K

X31

1	+ 24 V DC (UAL)
2	GND (UAR)
3	GND (UAL)
4	+ 24 V DC (UAR)