


Fibre optic through-beam sensor

FE-11-E-A-M3/F1x1/1m

Article no longer available - archive entry



Application

Function principle

Through-beam sensor

Detection zone

Range with fibre-optic amplifier type

OBF

OBF

Range of fibre optics

[mm]

200

Operating conditions

Ambient temperature

[°C]

-40...70

Mechanical data

Version of sensing head

straight

Sensing head thread

M3

Sensing head length

[mm]

20

Total length

[mm]

1000

Min. bending radius

[mm]

30

Fibre material

PMMA

Fibre head material

aluminium

Fibre sheath material

PE

E20602



Fibre optic through-beam sensor

FE-11-E-A-M3/F1x1/1m

Accessories	
Accessories (optional)	Cutter for fibre optics:, E20600
Remarks	
Pack quantity	1 pcs.