




Fibre optic diffuse reflection sensor

FT-30-P-A-E6/1M

Article no longer available - archive entry



| Application                           |                           |
|---------------------------------------|---------------------------|
| Function principle                    | Diffuse reflection sensor |
| Detection zone                        |                           |
| Range with fibre optic amplifier type | OIF                       |
| OIF                                   |                           |
| Range fibre optics [mm]               | 40                        |
| Operating conditions                  |                           |
| Ambient temperature [°C]              | -20...80                  |
| Mechanical data                       |                           |
| Version of sensing head               | straight                  |
| Sensing head diameter [mm]            | 6                         |
| Total length [mm]                     | 1000                      |
| Min. bending radius [mm]              | 30                        |
| Materials                             | Adapter: PA               |
| Fibre material                        | glass                     |
| Fibre head material                   | aluminium                 |
| Fibre sheath material                 | PVC                       |

E20289



Fibre optic diffuse reflection sensor

FT-30-P-A-E6/1M

Remarks

|               |        |
|---------------|--------|
| Pack quantity | 1 pcs. |
|---------------|--------|