




## Inductive sensor

IA-3010-BPOG/PPU

Article no longer available - archive entry



## Product characteristics

Electrical design		PNP
Output function		normally open
Sensing range	[mm]	10
Housing		cylindrical
Dimensions	[mm]	Ø 20

## Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	7; (24 V)
Protection class		II
Reverse polarity protection		no

## Outputs

Electrical design		PNP
Output function		normally open
Max. voltage drop switching output DC	[V]	1
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	100
Short-circuit protection		no
Overload protection		no

## Detection zone

Sensing range	[mm]	10
Real sensing range Sr	[mm]	10 ± 10 %
Operating distance	[mm]	0...8.1


# IA5044



## Inductive sensor

IA-3010-BPOG/PPU

Accuracy / deviations		
Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis [% of Sr]	1...15	
Switch point drift [% of Sr]	-10...10	
Operating conditions		
Ambient temperature [°C]	-25...80	
Protection	IP 67	
Tests / approvals		
EMC	EN 60947-5-2	
	EN 55011	class B
Mechanical data		
Housing	cylindrical	
Mounting	non-flush mountable	
Dimensions [mm]	Ø 20	
Materials	PBT	
Displays / operating elements		
Display	switching status	1 x LED, red
Accessories		
Accessories (supplied)	Mounting clamps: 1	
Remarks		
Pack quantity	1 pcs.	
Electrical connection		
Cable: 2 m, PUR / PVC; 3 x 0.5 mm <sup>2</sup>		
Connection		



Core colours :

BN = brown  
BU = blue  
BK = black

Article no longer available - archive entry