




Inductive sensor

II-2015-ARKG/UP/6M

Article no longer available - archive entry



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	15
Housing	threaded type
Dimensions [mm]	M30 x 1.5

Electrical data

Operating voltage [V]	10...55 DC
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	4.6
Minimum load current [mA]	4
Max. leakage current [mA]	0.5
Permanent current rating of switching output DC [mA]	400
Switching frequency DC [Hz]	200
Short-circuit protection	yes
Type of short-circuit protection	pulsed



Inductive sensor

II-2015-ARKG/UP/6M

Overload protection	yes
---------------------	-----

Detection zone	
----------------	--

Sensing range	[mm]	15
Real sensing range S_r	[mm]	$15 \pm 10 \%$
Operating distance	[mm]	0...12.1

Accuracy / deviations	
-----------------------	--

Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10

Operating conditions	
----------------------	--

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals		
-------------------	--	--

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data	
-----------------	--

Housing		threaded type
Mounting		non-flush mountable
Dimensions	[mm]	M30 x 1.5
Thread designation		M30 x 1.5
Materials		PBT

Displays / operating elements		
-------------------------------	--	--

Display	switching status	1 x LED, yellow
---------	------------------	-----------------

Accessories	
-------------	--

Items supplied	lock nuts: 2
----------------	--------------


Remarks	
---------	--

Pack quantity	1 pcs.
---------------	--------

Electrical connection	
-----------------------	--

Cable: 6 m, PVC; 2 x 0.34 mm²

Connection	
------------	--



BK = Core colours :
black