

IM5057




Inductive sensor

IMC3015-BPKG/US-100-DPS

Article no longer available - archive entry

Alternative articles: IM5115

When selecting an alternative article and accessories please note that technical data may differ!



Product characteristics

Electrical design	PNP
Output function	normally open
Sensing range [mm]	15
Housing	rectangular
Dimensions [mm]	40 x 40 x 66

Application

Special feature	Gold-plated contacts
-----------------	----------------------

Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	15; (24 V)
Protection class	II
Reverse polarity protection	yes

Outputs

Electrical design	PNP
-------------------	-----



Inductive sensor

IMC3015-BPKG/US-100-DPS

Output function		normally open	
Max. voltage drop switching output DC	[V]	2.5	
Permanent current rating of switching output DC	[mA]	250	
Switching frequency DC	[Hz]	300	
Short-circuit protection		yes	
Type of short-circuit protection		pulsed	
Overload protection		yes	
Detection zone			
Sensing range	[mm]	15	
Real sensing range Sr	[mm]	15 ± 10 %	
Operating distance	[mm]	0...12.1	
Accuracy / deviations			
Correction factor		steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of Sr]	1...15	
Switch point drift	[% of Sr]	-10...10	
Operating conditions			
Ambient temperature	[°C]	-25...70	
Protection		IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		rectangular	
Mounting		flush mountable	
Dimensions	[mm]	40 x 40 x 66	
Materials		housing: PBT; sensing face: PPE; clamp: PPS	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Accessories			
Items supplied		Mounting bracket: 1	
		Allen key: 1	
Remarks			
Remarks		5 positions of the active zone possible	
Pack quantity		1 pcs.	

IM5057



Inductive sensor

IMC3015-BPKG/US-100-DPS

Electrical connection - plug

Connector: 1 x M12; coding: A; Contacts: gold-plated



Connection

