




Inductive sensor

IO-2010-ARKG/ 6mPUR

Article no longer available - archive entry



1 Sensing face



Product characteristics

Electrical design	PNP/NPN
Output function	normally open
Sensing range [mm]	10
Housing	rectangular
Dimensions [mm]	26 x 26 x 70

Electrical data

Operating voltage [V]	10...55 DC
Reverse polarity protection	yes

Outputs

Electrical design	PNP/NPN
Output function	normally open
Max. voltage drop switching output DC [V]	6.5
Minimum load current [mA]	5
Max. leakage current [mA]	0.6
Permanent current rating of switching output DC [mA]	100
Switching frequency DC [Hz]	100
Short-circuit protection	yes
Type of short-circuit protection	pulsed



Inductive sensor

IO-2010-ARKG/ 6mPUR

Overload protection	yes
---------------------	-----

Detection zone

Sensing range	[mm]	10
Real sensing range S_r	[mm]	$10 \pm 10 \%$
Operating distance	[mm]	0...8.1

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.4 / copper: 0.3	
Hysteresis	[% of S_r]	1...15
Switch point drift	[% of S_r]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 68

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B

Mechanical data

Housing		rectangular
Mounting		flush mountable
Dimensions	[mm]	26 x 26 x 70
Materials		PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------


Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Cable: 6 m, PUR; 2 x 0.5 mm²

Connection



BK = Core colours :
black