


# KI5082



## Capacitive sensor

KI-3200NFAKGP2T/US



- 1 LED ring
- 2 programming buttons



### Product characteristics

Electrical design	PNP/NPN; (automatic load detection PNP/NPN)
Output function	normally open / normally closed; (selectable)
Sensing range [mm]	20
Communication interface	IO-Link
Housing	threaded type
Dimensions [mm]	M30 x 1.5 / L = 90

### Electrical data

Operating voltage [V]	10...36 DC
Current consumption [mA]	< 20
Protection class	II
Reverse polarity protection	yes
Measuring principle	capacitive

### Outputs

Electrical design	PNP/NPN; (automatic load detection PNP/NPN)
Output function	normally open / normally closed; (selectable)
Max. voltage drop switching output DC [V]	2.5
Permanent current rating of switching output DC [mA]	200
Switching frequency DC [Hz]	10
Short-circuit proof	yes
Overload protection	yes

### Detection zone

Sensing range [mm]	20
--------------------	----

### Accuracy / deviations

Hysteresis [% of Sr]	1...15
Switch point drift [% of Sr]	-20...20

### Interfaces

Communication interface	IO-Link
Transmission type	COM1 (4,8 kBaud)

# KI5082



## Capacitive sensor

KI-3200NFAKGP2T/US

IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Smart Sensor - SSP 0	Generic Profiled Sensor
	Function	Multiple switching signal
	Function	Process data variable
	Function	Teach channel
SIO mode	yes	
Min. process cycle time [ms]	100.8	
Supported DeviceIDs	<b>Type of operation</b>	<b>DeviceID</b>
	default	388

### Operating conditions

Ambient temperature [°C]	-25...80
Note on ambient temperature	temperature of the sensing face: -25...110 °C
Protection	IP 65; IP 67

### Tests / approvals

EMC	EN 61000-4-2 ESD	8 kV AD
	EN 61000-4-3 HF radiated	10 V/m
	EN 61000-4-4 Burst	2 kV
	EN 61000-4-6 HF conducted	3 V
	EN 55011	class B
Vibration resistance	EN 60068-2-6 Fc	(10...55 Hz) / 1 mm amplitude, oscillation period 5 min., 30 min. per axis at resonance or 55 Hz
Shock resistance	EN 60068-2-27 Ea	30 g 6 shocks / 11 ms half-sine (x, y, z)
MTTF [years]		569

### Mechanical data

Weight [g]	88.2
Housing	threaded type
Mounting	non-flush mountable
Dimensions [mm]	M30 x 1.5 / L = 90
Thread designation	M30 x 1.5
Materials	housing: PBT; pushbuttons: TPE-U; LED window: PC

### Displays / operating elements

Display	switching status	1 x LED, yellow
Teach function		yes
Electronic lock		yes

### Accessories

Items supplied	lock nuts: 2
----------------	--------------

### Remarks

Pack quantity	1 pcs.
---------------	--------

# KI5082





## Capacitive sensor

KI-3200NFAKGP2T/US

### Electrical connection - plug

Connector: 1 x M12; coding: A



4: OUT / IO-Link  
automatic load detection PNP/NPN  
when using a resistive load < 20 k $\Omega$