




Inductive sensor

IW-3008-ANOG/10m

Article no longer available - archive entry



Product characteristics

Electrical design		NPN
Output function		normally open
Sensing range [mm]		8
Housing		rectangular
Dimensions [mm]		60 x 36 x 10

Electrical data

Operating voltage [V]		10...36 DC
Current consumption [mA]		15; (24 V)
Protection class		II
Reverse polarity protection		no

Outputs

Electrical design		NPN
Output function		normally open
Max. voltage drop switching output DC [V]		1
Permanent current rating of switching output DC [mA]		250
Switching frequency DC [Hz]		120
Short-circuit protection		no
Overload protection		no

Detection zone

Sensing range [mm]		8
--------------------	--	---



Inductive sensor

IW-3008-ANOG/10m

Real sensing range Sr	[mm]	8 ± 10 %
Operating distance	[mm]	0...6.5

Accuracy / deviations

Correction factor	steel: 1 / stainless steel: 0.7 / brass: 0.4 / aluminium: 0.3 / copper: 0.2	
Hysteresis	[% of Sr]	1...15
Switch point drift	[% of Sr]	-10...10

Operating conditions

Ambient temperature	[°C]	-25...80
Protection		IP 67

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	1745

Mechanical data

Housing		rectangular
Mounting		non-flush mountable
Dimensions	[mm]	60 x 36 x 10
Materials		PBT

Displays / operating elements

Display	switching status	1 x LED, yellow
---------	------------------	-----------------


Remarks

Pack quantity		1 pcs.
---------------	--	--------

Electrical connection

Cable: 10 m, PVC; 3 x 0.14 mm²

Connection



Core colours :

BN = brown

BU = blue

BK = black