
O8S200

Through-beam sensor transmitter

O8S-OOKG/2,0M



1: light emission

Product characteristics		
Type of light		red light
Housing		rectangular
Application		
Function principle		Through-beam sensor
Electrical data		
Operating voltage	[V]	10...30 DC
Current consumption	[mA]	12; ((24 V))
Protection class		III
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	633
Detection zone		
Transmitter / receiver		transmitter
Range	[m]	< 3
Max. light spot diameter	[mm]	200
Light spot dimensions refer to		at maximum range

O8S200


Through-beam sensor transmitter

O8S-OOKG/2,0M

Operating conditions			
Ambient temperature	[°C]	-25...60	
Protection		IP 65; IP 67	
Tests / approvals			
EMC		EN 60947-5-2	
MTTF	[years]	2912	
UL approval		Ta	-25...60 °C
		Enclosure type	Type 1
		power supply	Limited Voltage/Current
		UL Approval no.	E027
		File number UL	E174191
Mechanical data			
Weight	[g]	40	
Housing		rectangular	
Dimensions	[mm]	28.1 x 8.1 x 14.4	
Materials		housing: ABS; stainless steel (1.4404 / 316L)	
Lens material		PMMA	
Lens alignment		side lens	
Displays / operating elements			
Display		switching status	1 x LED, yellow
		operation	1 x LED, green
Remarks			
Pack quantity		1 pcs.	
Electrical connection			

Cable: 2 m, PVC, black, Ø 2.9 mm; 2 x 0.08 mm²

Connection



	Core colours
BN	brown
BK	black
BU	blue


O8S200

Through-beam sensor transmitter

O8S-OOKG/2,0M

Diagrams and graphs

excess gain graph



x: distance [mm]

y: excess gain factor