



Diffuse reflection sensor

OPT-FPKG/TW3M

Article no longer available - archive entry

No scale drawing available

Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Function principle	Diffuse reflection sensor
--------------------	---------------------------

Electrical data

Operating voltage	[V]	10...55 DC
Current consumption	[mA]	12; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	880

Outputs

Electrical design		PNP
Output function		light-on/dark-on mode; (parameterisable)
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	400
Switching frequency DC	[Hz]	80
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range	[mm]	< 3000; (white paper 200 x 200 mm)
-------	------	------------------------------------

OP5030



Diffuse reflection sensor

OPT-FPKG/TW3M

Range adjustable		yes	
Operating conditions			
Ambient temperature		[°C]	-25...80
Protection		IP 65	
Tests / approvals			
EMC		EN 60947-5-2	
		EN 55011	class B
Mechanical data			
Housing		rectangular	
Dimensions		[mm]	86 x 28 x 142
Materials		PPO modified	
Lens material		glass	
Displays / operating elements			
Display		switching status	1 x LED, yellow
Remarks			
Pack quantity		1 pcs.	
Electrical connection			
terminals: ...1.5 mm²			
Connection			

