


Diffuse reflection sensor with background suppression

OTH-CNKG/US-100-DNX

Article no longer available - archive entry

Alternative articles: OT5214

When selecting an alternative article and accessories please note that technical data may differ!



receiver in lower lens
transmitter in upper lens

Product characteristics

Type of light	infrared light
Housing	rectangular

Application

Special feature	Background suppression
Function principle	Diffuse reflection sensor

Electrical data

Operating voltage	[V]	10...30 DC
Current consumption	[mA]	25; ((24 V))
Protection class		II
Reverse polarity protection		yes
Type of light		infrared light
Wave length	[nm]	950

Outputs

Electrical design		NPN
Output function		complementary
Max. voltage drop switching output DC	[V]	1.5
Permanent current rating of switching output DC	[mA]	100



Diffuse reflection sensor with background suppression

OTH-CNKG/US-100-DNX

Switching frequency DC	[Hz]	700
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone		
Range	[mm]	50...700; (white paper 200 x 200 mm)
Range adjustable		yes
Max. light spot diameter	[mm]	35
Light spot dimensions refer to		at maximum range
Background suppression available		yes

Operating conditions		
Ambient temperature	[°C]	-40...60
Protection		IP 65

Tests / approvals		
EMC	EN 60947-5-2	

Mechanical data		
Housing		rectangular
Dimensions	[mm]	75 x 17 x 33
Materials		Polycarbonat
Lens material		PMMA

Displays / operating elements		
Display	switching status	1 x LED, yellow

Accessories		
Items supplied	Angle bracket: 1, E20461	
	screwdrivers	

Remarks		
Pack quantity		1 pcs.

Electrical connection


Connector: 1 x M12; coding: A



Diffuse reflection sensor with background suppression


OTH-CNKG/US-100-DNX

Connection



Diagrams and graphs

accuracy graph



x: distance sensor/object [mm]

y: min. distance object/background [mm]

1 = object black (6 % remission) , background white (90 % remission)

2 = object grey (18 % remission) , background white (90 % remission)

3 = object white (90 % remission) , background white (90 % remission)

Note : range % = setting in % of the range