

OVP801





Video processing unit (VPU)

OVPAA/RO/E0/E1/NJ TX2/4GB/ODS

Article no longer available - archive entry

Alternative articles: OVP811

When selecting an alternative article and accessories please note that technical data may differ!



- 1 power supply / CAN interface
- 2 Ethernet 2 x RJ45
- 3 mini USB interface 2.0
- 4 USB interface 3.0
- 5 Connection cameras x 6 HFM



Application

Application ODS (obstacle detection) for collision avoidance

Electrical data

Operating voltage [V] 19.2...28.8 DC

Max. current consumption [mA] 3025; (625 + (n x 800) n = number of cameras)

OVP801



Video processing unit (VPU)

OVPA/RO/E0/E1/NJ TX2/4GB/ODS

Power consumption	[W]	40.8; (15 + n x 8,6; n = number of cameras)
Interfaces		
Number of CAN interfaces		1
Number of Ethernet interfaces		2
Number of USB interfaces		2
CAN		
Protocol		free protocol
Ethernet		
Transmission standard		1GBase-T
Transmission rate		1000 MBit/s
Connector type		RJ45
Protocol		TCP/IP
Factory settings		IP address: 192.168.0.69 subnet mask: 255.255.255.0 (Class C) gateway IP address: 192.168.0.201 MAC address: see type label
Sensor interface		
Transmission standard		FPD-Link
Connector type		HFM (Mini-FAKRA)
Note on interfaces		number of cameras when using the ODS function (Obstacles Detection System): see operating instructions
USB		
Connector type		Mini-USB; type A
Version		2.0; 3.0
Operating conditions		
Ambient temperature	[°C]	-10...40
Storage temperature	[°C]	-40...85
Protection		IP 50
Tests / approvals		
EMC	EN IEC 61000-6-4	radiation of interference / residential, commercial and light-industrial environments
	EN IEC 61000-6-2	immunity / industrial environments
Shock resistance	DIN EN 60068-2-27	50 g / (11 ms) not repetitive
	DIN EN 60068-2-27	40 g / (6 ms) repetitive
Vibration resistance	DIN EN 60068-2-6	2 g / (10...150 Hz)
	DIN EN 60068-2-64	2.3 g RMS / (10...500 Hz)
Electrical protection	DIN EN 61010-2-201	electrical supply only via PELV circuits
Mechanical data		
Weight	[g]	978.131
Dimensions	[mm]	126.5 x 29 x 180.4
Materials		housing: aluminium
Tightening torque	[Nm]	< 5.5

OVP801




Video processing unit (VPU)

OVPA A/RO/E0/E1/NJ TX2/4GB/ODS

Hardware	
Processor	CPU: Dual-Core NVIDIA Denver 2 64 Bit ; ARM Cortex A57; GPU: NVIDIA Pascal 256 CUDA Cores (1,3 TFLOPs) SOM: Nvidia Jetson TX2 4GB Module
RAM	4GB 128-bit LPDDR4, 1600 MHz - 51.2 GB/s
Mass storage	16GB eMMC 5.1 Flash

Remarks	
Pack quantity	1 pcs.


Electrical connection - Ethernet RJ45 connector



1	TX +
2	TX -
3	RX +
4	not used
5	not used
6	RX -
7	not used
8	not used

Electrical connection - USB socket

Connector: 1 x mini USB interface



Electrical connection - USB socket Typ A

Connector: 1 x Typ A



OVP801




Video processing unit (VPU)

OVPA A/RO/E0/E1/NJ TX2/4GB/ODS

Electrical connection - power supply / CAN

Connector: 1 x M12; coding: A



1	screen
2	24 V
3	GND
4	CAN +
5	CAN -

Electrical connection - sensor interface

Connector: 6 x HFM (Mini-FAKRA) (AMK12A-1M4Z5-A)

Other data

Connection

	Port 0	Port 1	Port 2	Port 3	Port 4	Port 5
example 1	camera 1 (3D-38k)	camera 2 (3D-38k)	camera 1 (2D)	camera 2 (2D)	camera 3 (3D-38k)	
example 2	camera 1 (2D)	camera 2 (2D)	camera 1 (3D-38k)	camera 2 (3D-38k)	camera 3 (2D)	camera 4 (2D)
example 3	camera 1 (3D-38k)	camera 2 (3D-38k)	----	camera 4 (3D- VGA)	----	

ports 0 and 1, 2 and 3, 4 and 5 must be assigned to the same type of image sensor.

please note the different 3D image sensor types 38k and VGA when connecting the cameras.

OVP801



Video processing unit (VPU)

OVPA/RO/E0/E1/NJ TX2/4GB/ODS

typical detection range

object / object height	camera heads	mounting position	typical detection range *
fork on ground	O3R225 105°	20...30 cm	1.3 m
	O3R225 105°	55...60 cm	1.5 m
	O3R222 60°	55...60 cm	2.5 m
fork cantilevered	O3R225 105°	20...30 cm	2.1 m
	O3R225 105°	55...60 cm	2.1 m
	O3R222 60°	55...60 cm	3.0 m
7 cm cube (18%)	O3R225 105°	20...30 cm	1.6 m
	O3R225 105°	55...60 cm	1.6 m
	O3R222 60°	55...60 cm	2.5 m

* test -conditions :

indoor

speed : ≤ 2 m/s

sealed, slightly inhomogeneous surface