
RB6015

Incremental encoder with solid shaft

RB-0500-I24/L2





RB6015

Incremental encoder with solid shaft

RB-0500-124/L2

Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (552000 Hz)
Mechanical data		
Weight	[g]	260.4
Dimensions	[mm]	Ø 35 / L = 52.5
Materials		aluminium
Max. revolution, mechanical [U/min]		10000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	6
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	5
Max. shaft load radial (at the shaft end)	[N]	10
Electrical connection		
Cable: 2 m, PUR; radial, can also be used axially		
brown A green 0 V A grey B pink 0 V B red 0 index black 0 V 0 index brown/green L+ (Up) white/green L- 0 V (Un) lilac failure inve screen housing		
Diagrams and graphs		
Pulse diagram		$\frac{1}{100}$