


RMA310



Absolute multiturn encoder with hollow shaft

MULTITURN ENCODER WET LINE



Product characteristics		
Resolution		65536 steps; 32768 revolutions; 31 bit
Communication interface		IO-Link
Shaft design		hollow shaft open to one side
Shaft diameter	[mm]	12
Application		
Function principle		absolute
Revolution type		multiturn
Detection system		magnetic
Electrical data		
Operating voltage	[V]	18...30 DC; (; to PELV)
Rated insulation voltage	[V]	30
Current consumption	[mA]	< 75
Protection class		III
Reverse polarity protection		yes
Max. power-on delay time	[ms]	1000
Max. revolution electrical	[U/min]	6000
Inputs		
Short-circuit protection digital inputs		yes
Measuring/setting range		
Resolution		65536 steps; 32768 revolutions; 31 bit
Accuracy / deviations		
Accuracy	[°]	0.1
Software / programming		
Parameter setting options		preset; zero point; direction of rotation; rotational speed
Interfaces		
Communication interface		IO-Link



Absolute multiturn encoder with hollow shaft

MULTITURN ENCODER WET LINE

Transmission type	COM3 (230,4 kBaud)	
IO-Link revision	1.1	
SDCI standard	IEC 61131-9 CDV	
Profiles	Function class	Designation
	0x4000	Identification and Diagnosis
	0x8001	Switching Signal Channel
	0x800B	Measurement Data Channel (high resolution)
SIO mode	no	
Required master port type	A	
Min. process cycle time [ms]	2.3	
IO-Link process data (cyclical)	function	bit length
	process value	96
	device status	4
	binary switching information	5
IO-Link functions (acyclical)	application specific tag; operating hours counter; internal temperature; switching cycles counter; shaft movement in hours	
Supported DeviceIDs	Type of operation	DeviceID
	default	1064
Note	For further information please see the IODD PDF file under "Downloads"	
Operating conditions		
Ambient temperature [°C]	-40...85	
Storage temperature [°C]	-40...85	
Max. relative air humidity [%]	98; (condensation not permissible)	
Protection	IP 68; IP 69K	
Tests / approvals		
EMC	DIN EN 61000-4-2 ESD	4 kV CD
	DIN EN 61000-4-3 HF radiated	10 V/m
	DIN EN 61000-4-4 Burst	2 kV
	DIN EN 61000-4-6 HF conducted	10 V
Vibration resistance	DIN EN 60068-2-6	20 g / 10...1000 Hz half-sine
Shock resistance	DIN EN 60068-2-27	200 g / 11 ms
Continuous shock resistance	DIN EN 60068-2-29	20 g / 6 ms half-sine
MTTF [years]	283	
UL approval	power supply	Class 2
Mechanical data		
Weight [g]	382.5	
Dimensions [mm]	Ø 42 / L = 89.5	
Materials	flange: stainless steel (316L/1.4404); housing: stainless steel (444/1.4521)	
Max. starting torque [Nm]	5	
Reference temperature torque [°C]	20	
Shaft design	hollow shaft open to one side	
Shaft diameter [mm]	12	
Shaft material	stainless steel (440B/1.4112)	
Installation depth of shaft [mm]	22	
Max. axial shaft misalignment [mm]	0,5	

RMA310




Absolute multiturn encoder with hollow shaft

MULTITURN ENCODER WET LINE

Fixing flange	Ø 42 mm
---------------	---------

Electrical connection - plug

Connector: 1 x M12; coding: A; Moulded body: stainless steel (316 / 1.4401)



1	UB
2	SSC1.2 / IN
3	GND
4	IO-Link
5	n. c.