
RN7004

Absolute singleturn encoder with solid shaft

RNK0013-C24/E

Article no longer available - archive entry

Alternative articles: RN7012
When selecting an alternative article and accessories please note that technical data may differ!



1 M4 Depth 5 mm

Product characteristics		
Resolution		8192 steps; 13 bit
Communication interface		CAN
Shaft design		solid shaft
Shaft diameter	[mm]	10
Application		
Function principle		absolute
Revolution type		singleturn
Electrical data		
Operating voltage	[V]	9...36 DC
Current consumption	[mA]	< 250
Reverse polarity protection		yes
Outputs		
Short-circuit protection		yes
Code		binary
Measuring/setting range		
Resolution		8192 steps; 13 bit
Accuracy / deviations		
Accuracy		± 1 LSB

RN7004

Absolute singleturn encoder with solid shaft

RNK0013-C24/E

Software / programming		
Parameter setting options		CAN parameter; scaling; preset; Baud rate; direction of rotation; address
Addressing		address selector switch; Software
Interfaces		
Communication interface		CAN
CAN		
Protocol		CANopen; DSP - 406
Operating conditions		
Ambient temperature	[°C]	-40...70
Protection		IP 66; (on the housing: IP 67; on the shaft: IP 66)
Tests / approvals		
Shock resistance		100 g (6 ms)
Vibration resistance		10 g (55...2000 Hz)
Mechanical data		
Weight	[g]	670
Dimensions	[mm]	Ø 58 / L = 100
Materials		aluminium
Max. revolution, mechanical	[U/min]	6000
Max. starting torque	[Nm]	1
Reference temperature torque	[°C]	20
Shaft design		solid shaft
Shaft diameter	[mm]	10
Shaft material		steel (1.4104)
Max. shaft load axial (at the shaft end)	[N]	10
Max. shaft load radial (at the shaft end)	[N]	20
Fixing flange		clamping flange

Electrical connection

terminal strip in the terminal chamber: ; Maximum cable length: 25 m; 100 m (500 kb/s)